

Motion[®] SP primax

Technical Data

7px

5px

3px

2px

1px



Hearing
Systems

SIEMENS

Motion SP primax | Features and Accessories

	7px	5px	3px	2px	1px
Audiology					
Signal processing (channels) / Gain/MPO (handles)	24 / 16	24 / 16	24 / 12	16 / 8	16 / 8
Hearing programs	6	6	6	4	4
SpeechMaster	●	●	●	●	●
HD Music (presets)	3	1	1	—	—
TwinPhone ¹⁾	●	●	●	—	—
EchoShield	●	—	—	—	—
Wireless CROS/BICROS ²⁾	●	●	●	—	—
Directionality (channels)	32	32	24	16	16
Narrow Directionality ¹⁾	■■■■■	■■■■	■■■	—	—
Directional microphone	■■■■■	■■■■	■■■	■■	■■
Spatial SpeechFocus ¹⁾	■■■■■	—	—	—	—
SpeechFocus	■■■■	■■■■	—	—	—
TruEar™	■■■■■	■■■■	■■■	—	—
Frequency compression	●	●	●	●	●
Extended bandwidth	—	—	—	—	—
Feedback cancellation	●	●	●	●	●
eWindScreen binaural ¹⁾	●	●	—	—	—
eWindScreen™ (steps)	3	3	on / off	on / off	—
Noise Reduction (channels / steps)	32 / 5	32 / 5	24 / 3	16 / 3	16 / on/off
Speech and noise management (steps)	7	5	3	3	on / off
SoundSmoothing™ (steps)	3	3	1	on / off	—
Directional speech enhancement (steps)	3	1	—	—	—
Adaptive streaming volume ³⁾	●	—	—	—	—
SoundBrilliance™ ³⁾	●	●	—	—	—
Sound equalizer (classes)	6	3	—	—	—
Spatial Configurator ¹⁾	●	●	—	—	—
Span ⁴⁾	●	●	—	—	—
Direction ⁵⁾	●	●	—	—	—
SoundBalance	●	●	●	●	●
Fitting					
Insitugram	●	●	●	●	●
Learning (classes) / Data logging	6 / ●	3 / ●	1 / ●	— / ●	— / ●
Acclimatization manager	●	●	●	●	●
Tinnitus					
Tinnitus therapy					
Static therapy signal (handles / presets)	16 / 5	16 / 5	12 / 5	4 / 1	—
Ocean Waves therapy signal (presets)	4	4	4	—	—
Notch therapy	●	●	●	—	—

Motion SP primax | Features and Accessories

Style Specific Features	7px / 5px / 3px	2px / 1px
Ingress Protection Rating	IP67	IP67
Telecoil	●	●
AutoPhone®	●	—
Charging contacts	—	—
Battery Size	675	675
Battery door on/off function	●	●
Nanocoated housing	●	●
e2e wireless® 3.0	●	●
Audio streaming with easyTek	●	●
User controls coupling via e2e	●	●
Wireless programming	●	●
Instrument configurations		
Flat cover	—	—
Rotary volume control	—	—
Push button	●	●
Rocker switch / flat cover	● / ○	● / ○
Color conversion kit	only top housing	only top housing
Battery door – direct audio input	○	○
Battery door – child lock	○	○
LED status indicator	●	●
Small earhook	○	○
Accessories		
miniPocket™	○	○
CROS Pure®	○	—
eCharger™	—	—
easyPocket™	○	○
easyTek™	○	○
TV Transmitter (req. easyTek)	○	○
Transmitter (req. easyTek)	○	○
VoiceLink™ (req. easyTek)	○	○
App		
easyTek App (req. easyTek)	○	○
touchControl™ App	○	○

● available ■■■■■ highest feature performance ○ optional — not available

¹⁾ req. bilateral fitting and e2e 3.0

²⁾ req. CROS Pure accessory

³⁾ streaming only, req. easyTek

⁴⁾ req. easyTek & easyTek App, touchControl App or Rocker switch

⁵⁾ req. easyTek & easyTek App or touchControl App